



TENDO WZS GZB-S




Dati tecnici

ID	D1 [mm]	D2 [mm]	D3 [mm]	D4 [mm]	L1 [mm]	L10 [mm]	Peso [kg]
0207655	3 mm	12	17	10	45	8	0.1
0207656	4 mm	12	17	10	45	8	0.1
0207657	5 mm	12	17	10	45	8	0.1
0207658	6 mm	12	17	10	45	8	0.1
0207659	7 mm	12	17	10	45	8	0.1
0207660	8 mm	12	17	10	45	8	0.1




Dati tecnici

ID	D1 [mm]	D2 [mm]	D3 [mm]	D4 [mm]	L1 [mm]	L10 [mm]	Peso [kg]
0207685	3 mm	20	25	16	51	10	0.1
0207686	4 mm	20	25	16	51	10	0.1
0207687	5 mm	20	25	16	51	10	0.1
0207688	6 mm	20	25	16	51	10	0.1
0207680	7 mm	20	25	16	51	10	0.1
0207689	8 mm	20	25	16	51	10	0.1
0207681	9 mm	20	25	16	51	10	0.1
0207690	10 mm	20	25	16	51	10	0.1
0207682	11 mm	20	27	18	51	10	0.1
0207691	12 mm	20	27	18	51	10	0.1
0207683	13 mm	20	27	18	51	10	0.1
0207694	14 mm	20	27	18	51	10	0.1
0207684	15 mm	20	27	18	51	10	0.1
0207692	16 mm	20	27	18	51	10	0.1




Dati tecnici

ID	D1 [mm]	D2 [mm]	D3 [mm]	D4 [mm]	L1 [mm]	L10 [mm]	Peso [kg]
0207710	3 mm	22	27	18	53.5	10	0.1
0207711	4 mm	22	27	18	53.5	10	0.1
0207712	5 mm	22	27	18	53.5	10	0.1
0207713	6 mm	22	27	18	53.5	10	0.1
0207714	7 mm	22	27	18	53.5	10	0.1
0207715	8 mm	22	27	18	53.5	10	0.1
0207716	9 mm	22	27	18	53.5	10	0.1
0207717	10 mm	22	27	18	53.5	10	0.1
0207718	11 mm	22	27	18	53.5	10	0.1
0207719	12 mm	22	27	18	53.5	10	0.1
0207720	13 mm	22	27	18	53.5	10	0.1
0207721	14 mm	22	27	18	53.5	10	0.1
0207722	15 mm	22	27	18	53.5	10	0.1
0207723	16 mm	22	27	18	53.5	10	0.1



Dati tecnici


ID	D1 [mm]	D2 [mm]	D3 [mm]	D4 [mm]	L1 [mm]	L10 [mm]	Peso [kg]
0207695	6 mm	32	37	20	60.5	19	0.3
0207696	8 mm	32	37	20	60.5	19	0.3
0207697	10 mm	32	37	20	60.5	19	0.3
0207698	12 mm	32	37	20	60.5	19	0.3
0207701	14 mm	32	37	20	60.5	19	0.3
0207699	16 mm	32	37	20	60.5	19	0.3
0207702	18 mm	32	39	22	60.5	19	0.3
0207700	20 mm	32	39	22	60.5	19	0.3
0207703	25 mm	32	44	27	60.5	19	0.3



Dati tecnici

ID	D1 [mm]	D2 [mm]	D3 [mm]	L1 [mm]	L2 [mm]	L3 [mm]	L10 [mm]	Peso [kg]
0207585	3 mm	20	22	59	50	3	5	0.1
0207586	4 mm	20	22	59	50	3	5	0.1
0207587	5 mm	20	22	59	50	3	5	0.1
0207588	6 mm	20	22	59	50	3	5	0.1
0207589	7 mm	20	22	59	50	3	5	0.1
0207590	8 mm	20	22	59	50	3	5	0.1
0207591	9 mm	20	22	59	50	3	5	0.1
0207592	10 mm	20	22	59	50	3	5	0.1
0207593	11 mm	20	22	59	50	3	5	0.1
0207594	12 mm	20	22	59	50	3	5	0.1
0207595	13 mm	20	22	59	50	3	5	0.1
0207596	14 mm	20	22	59	50	3	5	0.1
0207597	15 mm	20	22	59	50	3	5	0.1
0207598	16 mm	20	22	59	50	3	5	0.1
0207599	17 mm	20	22	59	50	3	5	0.1


Ulteriori misure e versioni personalizzate disponibili su richiesta
Design con attacco a baionetta



Dati tecnici

ID	D1 [mm]	D2 [mm]	D3 [mm]	L1 [mm]	L2 [mm]	L3 [mm]	L10 [mm]	Peso [kg]
0207605	6 mm	32	34	69	61.5	4	5	0.3
0207606	8 mm	32	34	69	61.5	4	5	0.3
0207607	10 mm	32	34	69	61.5	4	5	0.3
0207608	12 mm	32	34	69	61.5	4	5	0.3
0207609	14 mm	32	34	69	61.5	4	5	0.3
0207610	16 mm	32	34	69	61.5	4	5	0.3
0207611	18 mm	32	34	69	61.5	4	5	0.3
0207612	20 mm	32	34	69	61.5	4	5	0.3
0207613	25 mm	32	34	69	61.5	4	5	0.3


Ulteriori misure e versioni personalizzate disponibili su richiesta
Design con attacco a baionetta



Dati tecnici

ID	D1 [mm]	D2 [mm]	D3 [mm]	L1 [mm]	L2 [mm]	L3 [mm]	Peso [kg]
0207615	3 mm	12	14	50	37.5	3	0.1
0207616	4 mm	12	14	50	37.5	3	0.1
0207617	5 mm	12	14	50	37.5	3	0.1
0207618	6 mm	12	14	50	37.5	3	0.1
0207619	8 mm	12	14	50	37.5	3	0.1


Ulteriori misure e versioni personalizzate disponibili su richiesta
Design con attacco a baionetta



Dati tecnici

ID	D1 [mm]	D2 [mm]	D3 [mm]	L1 [mm]	L2 [mm]	L3 [mm]	Peso [kg]
0207625	3 mm	20	22	55.5	43	3	0.1
0207626	4 mm	20	22	55.5	43	3	0.1
0207628	6 mm	20	22	55.5	43	3	0.1
0207629	7 mm	20	22	55.5	43	3	0.1
0207630	8 mm	20	22	55.5	43	3	0.1
0207631	9 mm	20	22	55.5	43	3	0.1
0207632	10 mm	20	22	55.5	43	3	0.1
0207633	11 mm	20	22	55.5	43	3	0.1
0207634	12 mm	20	22	55.5	43	3	0.1
0207635	13 mm	20	22	55.5	43	3	0.1
0207636	14 mm	20	22	55.5	43	3	0.1
0207637	15 mm	20	22	55.5	43	3	0.1
0207638	16 mm	20	22	55.5	43	3	0.1
0207627	5 mm	20	22	55.5	43	3	0.1


Ulteriori misure e versioni personalizzate disponibili su richiesta
Design con attacco a baionetta



Dati tecnici

ID	D1 [mm]	D2 [mm]	D3 [mm]	L1 [mm]	L2 [mm]	L3 [mm]	Peso [kg]
0207645	6 mm	32	34	69	57.5	4	0.3
0207646	8 mm	32	34	69	57.5	4	0.3
0207647	10 mm	32	34	69	57.5	4	0.3
0207648	12 mm	32	34	69	57.5	4	0.3
0207649	14 mm	32	34	69	57.5	4	0.3
0207650	16 mm	32	34	69	57.5	4	0.3
0207651	18 mm	32	34	69	57.5	4	0.3
0207652	20 mm	32	34	69	57.5	4	0.3
0207653	25 mm	32	34	69	57.5	4	0.3

Ulteriori misure e versioni personalizzate disponibili su richiesta
Design con attacco a baionetta




Dati tecnici

ID	D1 [mm]	D2 [mm]	D3 [mm]	D4 [mm]	L1 [mm]	L2 [mm]	L10 [mm]	Peso [kg]
0207955	3 mm	12	16.5	3.5	45	42.5	2	0.1
0207956	4 mm	12	16.5	3.5	45	42.5	2	0.1
0207957	5 mm	12	16.5	3.5	45	42.5	2	0.1
0207958	6 mm	12	16.5	3.5	45	42.5	2	0.1
0207959	8 mm	12	16.5	3.5	45	42.5	2	0.1

Ulteriori misure e versioni personalizzate disponibili su richiesta

Esecuzione con foro di sicurezza radiale – per alimentazione interna del refrigerante/resistente al refrigerante fino a max. 80 bar


Concentricità: $\leq 0,003$ mm



Dati tecnici

ID	D1 [mm]	D2 [mm]	D3 [mm]	D4 [mm]	L1 [mm]	L2 [mm]	L10 [mm]	Peso [kg]
0207965	3 mm	20	24	4	50.5	43	2	0.1
0207966	4 mm	20	24	4	50.5	43	2	0.1
0207967	5 mm	20	24	4	50.5	43	2	0.1
0207968	6 mm	20	24	4	50.5	43	2	0.1
0207969	7 mm	20	24	4	50.5	43	2	0.1
0207970	8 mm	20	24	4	50.5	43	2	0.1
0207971	9 mm	20	24	4	50.5	43	2	0.1
0207972	10 mm	20	24	4	50.5	43	2	0.1
0207973	11 mm	20	24	4	50.5	43	2	0.1
0207974	12 mm	20	24	4	50.5	43	2	0.1
0207975	13 mm	20	24	4	50.5	43	2	0.1
0207976	14 mm	20	24	4	50.5	43	2	0.1
0207977	15 mm	20	24	4	50.5	43	2	0.1
0207978	16 mm	20	24	4	50.5	43	2	0.1

Ulteriori misure e versioni personalizzate disponibili su richiesta
Esecuzione con foro di sicurezza radiale – per alimentazione interna del refrigerante/resistente al refrigerante fino a max. 80 bar
Concentricità: ≤ 0,003 mm




Dati tecnici

ID	D1 [mm]	D2 [mm]	D3 [mm]	D4 [mm]	L1 [mm]	L2 [mm]	L10 [mm]	Peso [kg]
0207885	6 mm	22	25	4	50.5	46	2	0.2
0207886	8 mm	22	25	4	50.5	46	2	0.2
0207887	10 mm	22	25	4	50.5	46	2	0.2
0207888	12 mm	22	25	4	50.5	46	2	0.2
0207889	14 mm	22	25	4	50.5	46	2	0.2
0207890	16 mm	22	25	4	50.5	46	2	0.2

Ulteriori misure e versioni personalizzate disponibili su richiesta

Esecuzione con foro di sicurezza radiale – per alimentazione interna del refrigerante/resistente al refrigerante fino a max. 80 bar

Concentricità: $\leq 0,003$ mm



Dati tecnici

ID	D1 [mm]	D2 [mm]	D3 [mm]	D4 [mm]	L1 [mm]	L2 [mm]	L10 [mm]	Peso [kg]
0207985	6 mm	32	35.5	4	60.5	53.5	2	0.3
0207986	8 mm	32	35.5	4	60.5	53.5	2	0.3
0207987	10 mm	32	35.5	4	60.5	53.5	2	0.3
0207988	12 mm	32	35.5	4	60.5	53.5	2	0.3
0207989	14 mm	32	35.5	4	60.5	53.5	2	0.3
0207990	16 mm	32	35.5	4	60.5	53.5	2	0.3
0207991	18 mm	32	35.5	4	60.5	53.5	2	0.3
0207992	20 mm	32	35.5	4	60.5	53.5	2	0.3
0207993	25 mm	32	35.5	4	60.5	53.5	2	0.3

Ulteriori misure e versioni personalizzate disponibili su richiesta
Esecuzione con foro di sicurezza radiale – per alimentazione interna del refrigerante/resistente al refrigerante fino a max. 80 bar
Concentricità: ≤ 0,003 mm



SCHUNK SE & Co. KG

Spanntechnik

Greiftechnik

Automatisierungstechnik

Bahnhofstr. 106 - 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

CMS@de.schunk.com

schunk.com